

## Physical property table of eNOVA porous ceramic

Item	Numerical value/content
Material code	<b>CB8470VP</b>
Colour	<b>Black</b>
Sintering temperature (°C)	<b>More than 1200</b>
Density (g / cm <sup>3</sup> )	<b>1.5</b>
Shore Scleroscope (HD)	<b>82</b>
Average pore size (μm)	<b>1~2</b>
Porosity (%)	<b>40~60</b>
Surface Resistance (Ω)	<b>10<sup>7</sup>~10<sup>9</sup></b>
Ra value after grinding (μm)	3.55~6.71(*1)

\*1 : Because the ceramic surface porosity characteristics are different for each measurement, the highest and lowest values of the sampling are listed for reference.